



ACO Aquacon® Aviation Fuel Filter Cartridges

Remove Water and Dirt from Jet Fuel and Avgas Outside-to-In Flow Cartridges

- Free and emulsified water to less than 5 ppm
- 1/2 micrometer particulate removal
- Provides protection against “slugs” of water
- Pressure increase signals cartridge change
- Use with existing filter housings

DESCRIPTION

Patented* **Aquacon** Filter Cartridges have a unique high-capacity inner filter media which removes all free and emulsified water from hydrocarbon fuels down to less than 5 ppm in the effluent. Absorbed water is chemically locked into this media.

When a cartridge reaches its water holding capacity, its accordion pleats swell and cause an increase in the differential pressure which signals the operator to change the cartridge.

Solid contaminants are removed by the cartridge's two particulate filter media layers. The pleated accordion style design provides a large surface area for maximum dirt holding capacity. Models are offered for particulate filtration down to 1/2 micrometer size with 98% plus efficiency. Performance is not affected by the presence of common surface active agents.

Compact **Aquacon** Cartridges are quick and easy to install. Models are available to fit most existing standard housings. Refer to Cartridge Selection Table on reverse side.

*****CAUTION*****


DO NOT USE WITH PRE-MIXED FUELS CONTAINING ANTI-ICING ADDITIVES.

Use form 1846 for cartridge changeout at flowrates less than rated flow.



ACO-60901L

ACO-61401L



Typical Aquacon Cartridge Construction

* U.S. Patent No. 4,242,206.

CARTRIDGE SELECTION TABLE


Model Number	Micron Ratings	Inside Diameter (Inches)	Outside Diameter (Inches)	Length (Inches)	Collapse Pressure (psi)	Maximum Flow Rate (USGPM)	Interchange Information
ACO-21001L	0.5	1 ¹ / ₃₂	2 ⁵ / ₈	9 ³ / ₄	60	15	Fits VF-31E Housing
ACO-31001L	0.5	1 ⁷ / ₁₆	3	9 ³ / ₄	75	20	Fits Purolator Vessel PR-172-3
ACO-40501SPL	0.5	1-12NF	3 ³ / ₄	5 ¹ / ₂	60	10	Use with head SPH-2
ACO-40801L	0.5	1 ³ / ₄	4	8	100	13	Rellumit Replacement
ACO-40901SPL	0.5	1 ³ / ₈ - 12NF	3 ³ / ₄	8 ¹ / ₂	60	15	Use with head SPH-3
ACO-41201L	0.5	1 ³ / ₄	4	12 ¹ / ₄	100	20	Replaces Facet C-707; Purolator Vessel PAG-50
ACO-41601L	0.5	1 ³ / ₄	4	15 ¹³ / ₁₆	100	27	Rellumit Replacement
ACO-41801L	0.5	1 ³ / ₄	4	18	100	30	Replaces Facet C-706 and Keene BP-419, BP-518
ACO-41901L	0.5	1 ³ / ₄	4	19 ⁷ / ₈	175	32	Rellumit Replacement
ACO-51201L	0.5	1 ⁷ / ₈	5 ⁵ / ₈	12 ¹ / ₄	75	50	Fits VF-61 Housing
ACO-512P3L	0.3	1 ⁷ / ₈	5 ⁵ / ₈	12 ¹ / ₄	75	50	Fits VF-61 Housing
ACO-60801L	0.5	3 ¹ / ₂	6	8 ¹ / ₄	100	30	Omeco 6" x 8" Replacement
ACO-60901L	0.5	1 ¹ / ₂	6	9 ¹¹ / ₁₆	100	36	Fits Fram/Facet VFCS-21 (Element CC-21-7); VF-609
ACO-609P3L	0.3	1 ¹ / ₂	6	9 ⁹ / ₁₆	100	36	Fits Fram/Facet VFCS-21 (Element CC-21-7); VF-609
ACO-61201L	0.5	1 ¹ / ₂	6	13 ³ / ₄	100	48	Fits Fram/Facet VFCS-22 (Element CC-22-7)
ACO-61401L	0.5	3 ¹ / ₂	6	14 ¹ / ₂	175	58	Qualified to IP-1583
ACO-62201LTB	0.5	3 ¹ / ₂	6	22	175	88	Qualified to IP-1583
ACO-62901L	0.5	3 ¹ / ₂	6	28 ³ / ₄	175	115	Qualified to IP-1583
ACO-63301L	0.5	3 ¹ / ₂	6	33 ¹ / ₄	175	133	Qualified to IP-1583
ACO-64401L	0.5	3 ¹ / ₂	6	43 ¹ / ₄	175	173	Qualified to IP-1583
ACO-64401LTB	0.5	3 ¹ / ₂	6	44	175	176	Qualified to IP-1583
ACO-71801L	0.5	2 ¹ / ₂	6 ¹ / ₄	18	75	65	Fits VF-71E Housing

TECHNICAL INFORMATION

1. Maximum operating temperature is 160°F
2. Micron ratings are nominal at 98%+ efficiency
3. **Aquacon** Cartridges can significantly reduce flow when loaded with water or dirt. Appropriate precautions should be taken in applications where fuel flow must be maintained or where surge conditions can occur.

4. Replace the cartridge if the differential pressure exceeds 25 psid. For service life information, please refer to Operating Procedure # 1839 or consult your company fuel handling procedures.

NOTE: 1/2 micron rated **Aquacon** Cartridges are recommended for use with jet fuel and avgas. Effluent quality meets requirements for IP-1583.



Velcon products are sold and serviced by a world-wide representative network. To order, contact Headquarters or your **LOCAL REPRESENTATIVE:**

COMPANY HEADQUARTERS:
 Velcon Filters, Inc.
 1210 Garden of the Gods Road
 Colorado Springs, CO 80907-3410
 Phone: 1.800.531.0180 / 1.719.531.5855
 Fax: 719.531.5690
 e-mail: vfsales@velcon.com
 www.velcon.com

MANUFACTURING PLANTS LOCATED AT:
 Colorado Springs, Colorado
 Sylacauga, Alabama

OVERSEAS AFFILIATES:
 Frankfurt/M., Germany & Singapore

**Liquid Filtration
and Separation
Specialists**